



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



TY526M 11" "Ty-Rap" Cable Tie

Abb Installation Products, Inc

Catalog Number	TY526M
Manufacturer	Abb Installation Products, Inc
Description	Cable Tie, Natural Polyamide (Nylon 6.6) For Temperatures Up to 85 Degrees Celsius (185 F) For Indoor Applications, Length Of 281.94MM (11.10 Inches), Width Of 3.6MM (0.14 Inches), Tensile Strength Rating Of 134 Newtons (30 Pounds), Bulk
Weight per unit	0.0025 (lbs/each)
Product Category	Cable Ties & Wraps

Features

Bundle Diameter	0.08 to 2.99 in , 2 to 76 mm
Material	Nylon/Polyamide 6.6
Tensile Strength	30 pounds , 134 newtons

Material, Color, and Finish

Color	Ivory
-------	-------

Dimensions and Weight

Length	10.9 in , 277 mm
Thickness	0.04 in , 1.0 mm
Width	0.14 in , 3.6 mm

Descriptions

Description	11" "TY-RAP" CABLE TIE
extra long description	ABB TY526M CBL TIE 30LB 11.10 PO NA
Long Description	Cable Tie, Natural Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F) for Indoor Applications, Length of 281.94mm (11.10 Inches), Width of 3.6mm (0.14 Inches), Tensile Strength Rating of 134 Newtons (30 pounds), bulk
Product Type	CBL Tie 30LB 11.10 Po Nat Nylon
Special Features	Low profile head is designed to prevent snags on uneven surfaces and easier to pull through bulkheads. Non-magnetic stainless steel locking device insures both maximum strength and the right tightness every time

Manufacturer Information

Brand	Ty-Rap
GTIN	00786210825496
Manufacturers Part Number	TY526M
UPC	786210825496



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	Screws, Bolts, Staples, Jack Chains, Washers & TY-Raps
Type	HIGH PERFORMANCE

Packaging

Carton	100
Package	500
Weight Per each	0.0025

Uses, Certifications, and Standards

standard	UL E49405
----------	-----------