



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



WSXPDTDWH 0-10V Dual Tech Dimmer

Lithonia Lighting - Acuity

Catalog Number	WSXPDTDWH
Manufacturer	Lithonia Lighting - Acuity
Description	The WSX D Wall Switch Sensor With Dimming Has A Modern Low-Profile Appearance, Soft-Click Buttons and Small Motion Detection Up to 20 Feet (6.10 M), Making Them Ideal For Commercial and Residential Lighting Control Applications or Any Other Small Enclosed Spaces
Weight per unit	0.3200 (lbs/each)
Product Category	Lighting Occupancy Sensors

Features

average life	87,600
dimmable	Yes
Hardware	Yes
Material	Plastic
Power Source	Hardwired
Shape	Rectangular
Voltage Rating	120,277
Warranty	5

Material, Color, and Finish

Lens Material	Plastic
---------------	---------

Dimensions and Weight

Height	2.5
Length	5
Width	3

Descriptions

Description	0-10V DUAL TECH DIMMER
extra long description	LITH WSX PDT D WH Wall Switch Senso
Long Description	The WSX D Wall Switch Sensor with Dimming has a modern low-profile appearance, soft-click buttons and small motion detection up to 20 feet (6.10 m), making them ideal for commercial and residential lighting control applications or any other small enclosed spaces
Product Type	Sensor

Manufacturer Information

Brand	SENSOR SWITCH
GTIN	00889804540079
Manufacturers Part Number	WSX PDT D WH
UPC	889804540079



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description Fuses & Fuse Accessories

Packaging

Carton 1

Weight Per each 0.32

Uses, Certifications, and Standards

Application Education, Government, Healthcare, Hospitality, House of
Worship, Manufacturing, Offices & Banks, Retail, Sports and
Recreation, Warehouses

environmental conditions Indoor

Mounting Semi-recessed

standard cUL, UL