

Eaton XTOE020CCS

Catalog Number: XTOE020CCS

Eaton C440 electronic overload relay, XT IEC, 4-20A overload range, 45 mm Frame size, NO-NC contact configuration, Direct to contactor mounting, Selectable - 10A, 10, 20, 30 trip type

General specifications

Product Name	Catalog Number
Eaton C440 electronic overload relay	XTOE020CCS
UPC	Product Length/Depth
786685416472	1.8 in
Product Height	Product Width
4.3 in	1.42 in
Product Weight	Compliances
0.87 lb	ATEX Compliant
	RoHS Compliant
	CE Marked

Certifications

IEC 60947
CSA Certified
EN 60947
UL Listed



defaultTaxonomyAttributeLabel

Overload range

4-20A

Type

Electronic overload relay

Frame size

45 mm

Mounting method

Direct

Contact configuration

NO, NC

Trip type

Selectable 10 A, class 10 ,20, 30

Resources

Brochures

[C440 Electronic Overload Relay](#)

Catalogs

[Eaton's Volume 5—Motor Control and Protection](#)

Drawings

[XTOE_C AutoCAD 2D Footprint \(mm\)](#)

[XTOE_C 2D PDF](#)

[XTOE_C 2D Drawing Xchange](#)

[XTOE_C 3D Model Xchange](#)

[XTOE_C 3D Inventor](#)

[XTOE_C AutoCAD 2D Footprint](#)

Installation instructions

[XTOE/ZEB IEC Electronic Overload - Self Powered](#)

Specifications and datasheets

[Eaton Specification Sheet - XTOE020CCS](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

Eaton XTOE020CCS

Catalog Number: XTOE020CCS

Eaton C440 electronic overload relay, XT IEC, 4-20A overload range, 45 mm Frame size, NO-NC contact configuration, Direct to contactor mounting, Selectable - 10A, 10, 20, 30 trip type

General specifications

Product Name	Catalog Number
Eaton C440 electronic overload relay	XTOE020CCS
UPC	Product Length/Depth
786685416472	1.8 in
Product Height	Product Width
4.3 in	1.42 in
Product Weight	Compliances
0.87 lb	ATEX Compliant
	RoHS Compliant
	CE Marked
Certifications	
IEC 60947	
CSA Certified	
EN 60947	
UL Listed	



defaultTaxonomyAttributeLabel

Overload range

4-20A

Type

Electronic overload relay

Frame size

45 mm

Mounting method

Direct

Contact configuration

NO, NC

Trip type

Selectable 10 A, class 10 ,20, 30

Resources

Brochures

[C440 Electronic Overload Relay](#)

Catalogs

[Eaton's Volume 5—Motor Control and Protection](#)

Drawings

[XTOE_C AutoCAD 2D Footprint \(mm\)](#)

[XTOE_C 2D PDF](#)

[XTOE_C 2D Drawing Xchange](#)

[XTOE_C 3D Model Xchange](#)

[XTOE_C 3D Inventor](#)

[XTOE_C AutoCAD 2D Footprint](#)

Installation instructions

[XTOE/ZEB IEC Electronic Overload - Self Powered](#)

Specifications and datasheets

[Eaton Specification Sheet - XTOE020CCS](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia