



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## UAG12 1/2" Ua Sealtite Conduit, Bonded UI 100'

*Southwire Company*

Catalog Number	UAG12
Manufacturer	Southwire Company
Description	Liquidtight Flexible Conduit, 1/2 In Trade Size, 0.82 to 0.84 In Conduit Outer Diameter, 0.622 to 0.642 In Conduit Inner Diameter, TITAN2(TM) UI Style, 100 FT Length, Jacket: Thermoplastic;Core: Steel, Hot Dip Galvanized, Gray, 4 In Bend Radius, -67 °F Operating Temperature, +176 °F Operating Temperature, 30 LB/100 FT
Weight per unit	0.3000 (lbs/ft)
Product Category	Liquid Tight Conduit

### Features

outside diameter	830
------------------	-----

### Descriptions

Description	1/2" UA SEALTITE CONDUIT, BONDED UL 100'
extra long description	SWC 55082603 Titan2 Type UL Liquidt

### Manufacturer Information

GTIN	00032886042317
UPC	032886042317

### Taxonomies, Classifications, and Categories

Category Description	Liquid Tight
Type	LTM-UL

### Packaging

Carton	100
Weight Per foot	0.3