



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## YA30 300 Comp Lug 1/2" Stud Hole

Burndy LLC

Catalog Number	YA30
Manufacturer	Burndy LLC
Description	300 Kcmil Cu, One Hole, 1/2 Stud Size, Long Barrel, Internal Chamfer, Tin Plated, UL/Csa, 90 C, Up to 35KV, White Color Code, 17 or 298 Die Index.
Weight per unit	0.2100 (lbs/each)
Product Category	Large Terminals & Connectors

### Features

Die Index	17
Material	Copper
Voltage Rating	35

### Material, Color, and Finish

Color Code	WHITE
------------	-------

### Descriptions

Description	300 COMP LUG 1/2" STUD HOLE
extra long description	BUR YA30 300 CU 1-HOLE LONG 1/2
Long Description	300 kcmil CU, One Hole, 1/2 Stud Size, Long Barrel, Internal Chamfer, Tin Plated, UL/CSA, 90 C, Up to 35kV, WHITE Color Code, 17 or 298 Die Index.
Product Type	Terminal
Special Features	Features: UL Listed 90 DEG C, 600 V - 35 KV, 45 DEG And 90 DEG Angles Are Available, Finish: Electro-Tin Plated, Tongue Angle: Straight, Temperature Rating: 90 DEG C, Wire Strip Length: 2 IN, Die Index: 17 Or 298, Color Code: White, Tools, Die Set Catalog Number, And (number Of Crimps): Mechanical: MD6, OUR840, MD7-34R Tool, W30VT Die, (4), Hydraulic: BCT500HS, Y500CTHS Tool, W30VT, W30RT Die, (4), Y35, Y39, Y750, PAT750 Tool, U30RT, U28ART Die, (4), Y46 Tool, U30RT, U28ART Die With PUADP-1 Adapter, (4), C

### Manufacturer Information

Brand	BURNDY
GTIN	00781810504550
Manufacturers Part Number	YA30
UPC	781810504550

### Taxonomies, Classifications, and Categories

Category Description	Comp & Mech Lugs and Butt Splices
Type	Long Barrel, Tin Plated



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Package	10
Weight Per each	0.21

## Uses, Certifications, and Standards

Application	Wire Termination
standard	UL 486A-486B