



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



YA26LBOX 2/0 Cu 1H Short 3/8

Burndy LLC

Catalog Number	YA26LBOX
Manufacturer	Burndy LLC
Description	2/0 Awg Cu, One Hole, 3/8 Stud Size, Standard Barrel, Inspection Window, Internal Chamfer, Tin Plated, UI/Csa 90 Up to 35KV, Black Color Code, 13 Die Index.
Weight per unit	0.0600 (lbs/each)
Product Category	Large Terminals & Connectors

Features

Die Index	13
Material	Copper
Voltage Rating	35

Material, Color, and Finish

Color Code	BLACK
------------	-------

Descriptions

Description	2/0 CU 1H SHORT 3/8
extra long description	BUR YA26LBOX 2/0 CU 1-HOLE SHORT 3/
Long Description	2/0 AWG CU, One Hole, 3/8 Stud Size, Standard Barrel, Inspection Window, Internal Chamfer, Tin Plated, UL/CSA 90 Up to 35kV, BLACK Color Code, 13 Die Index.
Product Type	Terminal
Special Features	Features: UL Listed 90 DEG C, 600 V To 35 KV 45 DEG, 90 DEG Angles Are Available, Tools, Die Set Catalog Number, And (number Of Crimps): MD6, OUR840, MD7-34R Mechanical: W26VT (2), W26RT (2), X26RT (2),BCT500HS, Y500CTHS Hydraulic: W26VT (2),W26RT (2), X25RT (2), X26RT (2), Y35, Y39, Y750, Y46, PAT750 Hydraulic:U26RT (1), Dieless: MY29-3 (1), MY29-11 (1), MRC840 (2), Y644HS (1), Y81KFT (1), Y81KFTMBH (1), PAT81KFT-18V (1), Wire Strip Length: 1 IN, Conductor Type: Commercial Stranded Copper, Tongue Angle: S

Manufacturer Information

Brand	BURNDY
GTIN	00781810553756
Manufacturers Part Number	YA26LBOX
UPC	781810553756

Taxonomies, Classifications, and Categories

Category Description	Comp & Mech Lugs and Butt Splices
Type	Standard Barrel, Tin Plated



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton 10

Weight Per each 0.06

Uses, Certifications, and Standards

Application Wire Termination

standard UL 486A-486B