



Safety Data Sheet

Copyright, 2016, 3M Company.

All rights reserved. Copying and/or downloading of this information for the purpose of properly utilizing 3M products is allowed provided that: (1) the information is copied in full with no changes unless prior written agreement is obtained from 3M, and (2) neither the copy nor the original is resold or otherwise distributed with the intention of earning a profit thereon.

Document Group:	26-4367-4	Version Number:	5.00
Issue Date:	01/07/16	Supersedes Date:	05/27/15

Product identifier

5514A SERIES QSIII SPLICE KITS

ID Number(s):

80-6112-0750-9, 80-6112-0751-7, 80-6112-0752-5, 80-6112-0753-3, 80-6112-0754-1, 80-6112-0755-8, 80-6112-0756-6, 80-6114-3751-0, 80-6114-3752-8

Recommended use

Electrical

Supplier's details

MANUFACTURER:	3M
DIVISION:	Electrical Markets Division
ADDRESS:	3M Center, St. Paul, MN 55144-1000, USA
Telephone:	1-888-3M HELPS (1-888-364-3577)

Emergency telephone number

1-800-364-3577 or (651) 737-6501 (24 hours)

This product is a kit or a multipart product which consists of multiple, independently packaged components. A Safety Data Sheet (SDS), Article Information Sheet (AIS), or Article Information Letter (AIL) for each of these components is included. Please do not separate the component documents from this cover page. The document numbers for components of this product are:

06-4861-8, 11-4628-1, 34-7684-3

DISCLAIMER: The information in this Safety Data Sheet (SDS) is believed to be correct as of the date issued. 3M MAKES NO WARRANTIES, EXPRESSED OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR COURSE OF PERFORMANCE OR USAGE OF TRADE. User is responsible for determining whether the 3M product is fit for a particular purpose and suitable for user's method of use or application. Given the variety of factors that can affect the use and application of a 3M product, some of which are uniquely within the user's knowledge and control, it is essential that the user evaluate the 3M product to determine whether it is fit for a particular purpose and suitable for user's method of use or application.

3M provides information in electronic form as a service to its customers. Due to the remote possibility that electronic transfer may have resulted in errors, omissions or alterations in this information, 3M makes no representations as to its completeness or accuracy. In addition, information obtained from a database may not be as current as the information in the SDS available directly from 3M

3M USA SDSs are available at www.3M.com



Safety Data Sheet

Copyright,2018,3M Company.

All rights reserved. Copying and/or downloading of this information for the purpose of properly utilizing 3M products is allowed provided that: (1) the information is copied in full with no changes unless prior written agreement is obtained from 3M, and (2) neither the copy nor the original is resold or otherwise distributed with the intention of earning a profit thereon.

Document Group:	06-4861-8	Version Number:	12.01
Issue Date:	07/25/18	Supersedes Date:	02/19/18

SECTION 1: Identification

1.1. Product identifier

3M™ P55/R Lubricant, Red

Product Identification Numbers

ID Number	UPC	ID Number	UPC
78-8096-4318-8		78-8126-9891-4	
80-6116-0479-6			

1.2. Recommended use and restrictions on use

Recommended use

Electrical, ELECTRICAL LUBRICATING GREASE

1.3. Supplier's details

MANUFACTURER:	3M
DIVISION:	Electrical Markets Division
ADDRESS:	3M Center, St. Paul, MN 55144-1000, USA
Telephone:	1-888-3M HELPS (1-888-364-3577)

1.4. Emergency telephone number

1-800-364-3577 or (651) 737-6501 (24 hours)

SECTION 2: Hazard identification

2.1. Hazard classification

Not classified as hazardous according to OSHA Hazard Communication Standard, 29 CFR 1910.1200.

2.2. Label elements

Signal word

Not applicable.

Symbols

Not applicable.

Pictograms

Not applicable.

Precautionary Statements

Disposal:

Dispose of contents/container in accordance with applicable local/regional/national/international regulations.

95% of the mixture consists of ingredients of unknown acute inhalation toxicity.

SECTION 3: Composition/information on ingredients

Ingredient	C.A.S. No.	% by Wt
1,1,2,3,3,3-HEXAFLUORO-1-PROPENE, OXIDIZED, POLYMD.	69991-67-9	95 - 98
SYNTHETIC AMORPHOUS SILICA, FUMED, CRYSTALLINE FREE	112945-52-5	<= 5
C.I. PIGMENT RED 170	2786-76-7	<= 0.05

SECTION 4: First aid measures

4.1. Description of first aid measures

Inhalation:

Remove person to fresh air. If you feel unwell, get medical attention.

Skin Contact:

Wash with soap and water. If signs/symptoms develop, get medical attention.

Eye Contact:

Flush with large amounts of water. Remove contact lenses if easy to do. Continue rinsing. If signs/symptoms persist, get medical attention.

If Swallowed:

No need for first aid is anticipated.

4.2. Most important symptoms and effects, both acute and delayed

See Section 11.1. Information on toxicological effects.

4.3. Indication of any immediate medical attention and special treatment required

Not applicable.

SECTION 5: Fire-fighting measures

5.1. Suitable extinguishing media

In case of fire: Use a fire fighting agent suitable for ordinary combustible material such as water or foam to extinguish.

5.2. Special hazards arising from the substance or mixture

None inherent in this product.

Hazardous Decomposition or By-Products

Substance

Carbonyl Fluoride
Carbon monoxide
Carbon dioxide

Condition

During Combustion
During Combustion
During Combustion

Hydrogen Fluoride
Oxides of Nitrogen

During Combustion
During Combustion

5.3. Special protective actions for fire-fighters

When fire fighting conditions are severe and total thermal decomposition of the product is possible, wear full protective clothing, including helmet, self-contained, positive pressure or pressure demand breathing apparatus, bunker coat and pants, bands around arms, waist and legs, face mask, and protective covering for exposed areas of the head.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Evacuate area. Ventilate the area with fresh air. For large spill, or spills in confined spaces, provide mechanical ventilation to disperse or exhaust vapors, in accordance with good industrial hygiene practice. Refer to other sections of this SDS for information regarding physical and health hazards, respiratory protection, ventilation, and personal protective equipment.

6.2. Environmental precautions

Avoid release to the environment.

6.3. Methods and material for containment and cleaning up

Working from around the edges of the spill inward, cover with bentonite, vermiculite, or commercially available inorganic absorbent material. Mix in sufficient absorbent until it appears dry. Remember, adding an absorbent material does not remove a physical, health, or environmental hazard. Collect as much of the spilled material as possible. Place in a closed container approved for transportation by appropriate authorities. Clean up residue with an appropriate solvent selected by a qualified and authorized person. Ventilate the area with fresh air. Read and follow safety precautions on the solvent label and SDS. Seal the container. Dispose of collected material as soon as possible in accordance with applicable local/regional/national/international regulations.

SECTION 7: Handling and storage

7.1. Precautions for safe handling

For industrial or professional use only. Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Avoid release to the environment. Keep away from reactive metals (eg. Aluminum, zinc etc.) to avoid the formation of hydrogen gas that could create an explosion hazard.

7.2. Conditions for safe storage including any incompatibilities

Store away from acids. Store away from strong bases.

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

Occupational exposure limits

If a component is disclosed in section 3 but does not appear in the table below, an occupational exposure limit is not available for the component.

Ingredient	C.A.S. No.	Agency	Limit type	Additional Comments
SILICA, AMORPHOUS	112945-52-5	OSHA	TWA concentration:0.8 mg/m ³ ;TWA:20 millions of particles/cu. ft.	

ACGIH : American Conference of Governmental Industrial Hygienists

AIHA : American Industrial Hygiene Association

CMRG : Chemical Manufacturer's Recommended Guidelines

OSHA : United States Department of Labor - Occupational Safety and Health Administration

TWA: Time-Weighted-Average

STEL: Short Term Exposure Limit

CEIL: Ceiling

8.2. Exposure controls

8.2.1. Engineering controls

Use general dilution ventilation and/or local exhaust ventilation to control airborne exposures to below relevant Exposure Limits and/or control dust/fume/gas/mist/vapors/spray. If ventilation is not adequate, use respiratory protection equipment.

8.2.2. Personal protective equipment (PPE)

Eye/face protection

None required.

Skin/hand protection

No chemical protective gloves are required.

Respiratory protection

An exposure assessment may be needed to decide if a respirator is required. If a respirator is needed, use respirators as part of a full respiratory protection program. Based on the results of the exposure assessment, select from the following respirator type(s) to reduce inhalation exposure:

Half facepiece or full facepiece air-purifying respirator suitable for particulates

For questions about suitability for a specific application, consult with your respirator manufacturer.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

General Physical Form:	Liquid
Specific Physical Form:	Paste
Odor, Color, Grade:	ODORLESS, RED COLOR, GREASE
Odor threshold	<i>Not Applicable</i>
pH	<i>Not Applicable</i>
Melting point	<i>Not Applicable</i>
Boiling Point	270 °C [<i>Details</i> :MITS data (per supplier info)]
Flash Point	Flash point > 93 °C (200 °F)
Evaporation rate	<i>No Data Available</i>
Flammability (solid, gas)	Not Applicable
Flammable Limits(LEL)	<i>Not Applicable</i>
Flammable Limits(UEL)	<i>Not Applicable</i>
Vapor Pressure	<=0.01 mmHg
Vapor Density	<i>No Data Available</i>
Density	<i>No Data Available</i>
Specific Gravity	Approximately 1.99 Units not avail. or not appl. [<i>Ref Std</i> :WATER=1]
Solubility in Water	Nil
Solubility- non-water	<i>Not Applicable</i>
Partition coefficient: n-octanol/ water	<i>No Data Available</i>
Autoignition temperature	<i>Not Applicable</i>
Decomposition temperature	<i>Not Applicable</i>
Viscosity	<i>No Data Available</i>
Average particle size	<i>No Data Available</i>
Bulk density	<i>No Data Available</i>
Hazardous Air Pollutants	<i>No Data Available</i>

Molecular weight	No Data Available
Volatile Organic Compounds	No Data Available
Percent volatile	0.00 %
Softening point	No Data Available
VOC Less H2O & Exempt Solvents	No Data Available

SECTION 10: Stability and reactivity

10.1. Reactivity

This material may be reactive with certain agents under certain conditions - see the remaining headings in this section.

10.2. Chemical stability

Stable.

10.3. Possibility of hazardous reactions

Hazardous polymerization will not occur.

10.4. Conditions to avoid

Not determined

10.5. Incompatible materials

Strong acids
Strong bases
Reactive metals

No Data Available

10.6. Hazardous decomposition products

<u>Substance</u>	<u>Condition</u>
None known.	

Refer to section 5.2 for hazardous decomposition products during combustion.

Extreme heat arising from situations such as misuse or equipment failure can generate hydrogen fluoride as a decomposition product.

SECTION 11: Toxicological information

The information below may not be consistent with the material classification in Section 2 if specific ingredient classifications are mandated by a competent authority. In addition, toxicological data on ingredients may not be reflected in the material classification and/or the signs and symptoms of exposure, because an ingredient may be present below the threshold for labeling, an ingredient may not be available for exposure, or the data may not be relevant to the material as a whole.

11.1. Information on Toxicological effects

Signs and Symptoms of Exposure

Based on test data and/or information on the components, this material may produce the following health effects:

Inhalation:

May be harmful if inhaled.

Skin Contact:

Contact with the skin during product use is not expected to result in significant irritation.

Eye Contact:

Contact with the eyes during product use is not expected to result in significant irritation.

Ingestion:

No known health effects.

Toxicological Data

If a component is disclosed in section 3 but does not appear in a table below, either no data are available for that endpoint or the data are not sufficient for classification.

Acute Toxicity

Name	Route	Species	Value
Overall product	Inhalation-Dust/Mist(4 hr)		No data available; calculated ATE5 - 12.5 mg/l
Overall product	Ingestion		No data available; calculated ATE >5,000 mg/kg
SYNTHETIC AMORPHOUS SILICA, FUMED, CRYSTALLINE FREE	Dermal	Rabbit	LD50 > 5,000 mg/kg
SYNTHETIC AMORPHOUS SILICA, FUMED, CRYSTALLINE FREE	Inhalation-Dust/Mist (4 hours)	Rat	LC50 > 0.691 mg/l
SYNTHETIC AMORPHOUS SILICA, FUMED, CRYSTALLINE FREE	Ingestion	Rat	LD50 > 5,110 mg/kg

ATE = acute toxicity estimate

Skin Corrosion/Irritation

Name	Species	Value
SYNTHETIC AMORPHOUS SILICA, FUMED, CRYSTALLINE FREE	Rabbit	No significant irritation

Serious Eye Damage/Irritation

Name	Species	Value
SYNTHETIC AMORPHOUS SILICA, FUMED, CRYSTALLINE FREE	Rabbit	No significant irritation

Skin Sensitization

Name	Species	Value
SYNTHETIC AMORPHOUS SILICA, FUMED, CRYSTALLINE FREE	Human and animal	Not classified

Respiratory Sensitization

For the component/components, either no data are currently available or the data are not sufficient for classification.

Germ Cell Mutagenicity

Name	Route	Value
SYNTHETIC AMORPHOUS SILICA, FUMED, CRYSTALLINE FREE	In Vitro	Not mutagenic

Carcinogenicity

Name	Route	Species	Value
SYNTHETIC AMORPHOUS SILICA, FUMED, CRYSTALLINE FREE	Not Specified	Mouse	Some positive data exist, but the data are not sufficient for classification

Reproductive Toxicity**Reproductive and/or Developmental Effects**

Name	Route	Value	Species	Test Result	Exposure Duration
SYNTHETIC AMORPHOUS SILICA, FUMED, CRYSTALLINE FREE	Ingestion	Not classified for female reproduction	Rat	NOAEL 509 mg/kg/day	1 generation
SYNTHETIC AMORPHOUS SILICA, FUMED, CRYSTALLINE FREE	Ingestion	Not classified for male reproduction	Rat	NOAEL 497 mg/kg/day	1 generation
SYNTHETIC AMORPHOUS SILICA, FUMED, CRYSTALLINE FREE	Ingestion	Not classified for development	Rat	NOAEL 1,350 mg/kg/day	during organogenesis

Target Organ(s)**Specific Target Organ Toxicity - single exposure**

For the component/components, either no data are currently available or the data are not sufficient for classification.

Specific Target Organ Toxicity - repeated exposure

Name	Route	Target Organ(s)	Value	Species	Test Result	Exposure Duration
SYNTHETIC AMORPHOUS SILICA, FUMED, CRYSTALLINE FREE	Inhalation	respiratory system silicosis	Not classified	Human	NOAEL Not available	occupational exposure

Aspiration Hazard

For the component/components, either no data are currently available or the data are not sufficient for classification.

Please contact the address or phone number listed on the first page of the SDS for additional toxicological information on this material and/or its components.

SECTION 12: Ecological information**Ecotoxicological information**

Please contact the address or phone number listed on the first page of the SDS for additional ecotoxicological information on this material and/or its components.

Chemical fate information

Please contact the address or phone number listed on the first page of the SDS for additional chemical fate information on this material and/or its components.

SECTION 13: Disposal considerations**13.1. Disposal methods**

Dispose of contents/ container in accordance with the local/regional/national/international regulations.

Incinerate in a permitted waste incineration facility. Proper destruction may require the use of additional fuel during incineration processes. Combustion products will include HF. Facility must be capable of handling halogenated materials. Empty drums/barrels/containers used for transporting and handling hazardous chemicals (chemical substances/mixtures/preparations classified as Hazardous as per applicable regulations) shall be considered, stored, treated & disposed of as hazardous wastes unless otherwise defined by applicable waste regulations. Consult with the respective regulating authorities to determine the available treatment and disposal facilities.

EPA Hazardous Waste Number (RCRA): Not regulated

SECTION 14: Transport Information

For Transport Information, please visit <http://3M.com/Transportinfo> or call 1-800-364-3577 or 651-737-6501.

SECTION 15: Regulatory information

15.1. US Federal Regulations

Contact 3M for more information.

EPCRA 311/312 Hazard Classifications:

Physical Hazards

Not applicable

Health Hazards

Not applicable

15.2. State Regulations

Contact 3M for more information.

15.3. Chemical Inventories

The components of this material are in compliance with the provisions of Australia National Industrial Chemical Notification and Assessment Scheme (NICNAS). Certain restrictions may apply. Contact the selling division for additional information.

The components of this product are in compliance with the new substance notification requirements of CEPA.

The components of this product are in compliance with the chemical notification requirements of TSCA. All required components of this product are listed on the active portion of the TSCA Inventory.

Contact 3M for more information.

15.4. International Regulations

Contact 3M for more information.

This SDS has been prepared to meet the U.S. OSHA Hazard Communication Standard, 29 CFR 1910.1200.

SECTION 16: Other information

NFPA Hazard Classification

Health: 3 Flammability: 1 Instability: 0 Special Hazards: None

National Fire Protection Association (NFPA) hazard ratings are designed for use by emergency response personnel to address the hazards that are presented by short-term, acute exposure to a material under conditions of fire, spill, or similar emergencies. Hazard ratings are primarily based on the inherent physical and toxic properties of the material but also include the toxic properties of combustion or decomposition products that are known to be generated in significant quantities.

The NFPA Health code of 3 is due to emergency situations where the material may thermally decompose and release Hydrogen Fluoride. During normal use conditions, please reference Section 2 and Section 11 of the SDS for additional health hazard information.

HMIS Hazard Classification

Health: 0 Flammability: 1 Physical Hazard: 0 Personal Protection: X - See PPE section.

Hazardous Material Identification System (HMIS® IV) hazard ratings are designed to inform employees of chemical hazards

in the workplace. These ratings are based on the inherent properties of the material under expected conditions of normal use and are not intended for use in emergency situations. HMIS® IV ratings are to be used with a fully implemented HMIS® IV program. HMIS® is a registered mark of the American Coatings Association (ACA).

Document Group:	06-4861-8	Version Number:	12.01
Issue Date:	07/25/18	Supersedes Date:	02/19/18

Reason for Reissue

Conversion to GHS format SDS.

DISCLAIMER: The information in this Safety Data Sheet (SDS) is believed to be correct as of the date issued. 3M MAKES NO WARRANTIES, EXPRESSED OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR COURSE OF PERFORMANCE OR USAGE OF TRADE. User is responsible for determining whether the 3M product is fit for a particular purpose and suitable for user's method of use or application. Given the variety of factors that can affect the use and application of a 3M product, some of which are uniquely within the user's knowledge and control, it is essential that the user evaluate the 3M product to determine whether it is fit for a particular purpose and suitable for user's method of use or application.

3M provides information in electronic form as a service to its customers. Due to the remote possibility that electronic transfer may have resulted in errors, omissions or alterations in this information, 3M makes no representations as to its completeness or accuracy. In addition, information obtained from a database may not be as current as the information in the SDS available directly from 3M.

3M USA SDSs are available at www.3M.com



Article Information Sheet

Copyright, 2017, 3M Company.

All rights reserved. Copying and/or downloading of this information for the purpose of properly utilizing 3M products is allowed provided that: (1) the information is copied in full with no changes unless prior written agreement is obtained from 3M, and (2) neither the copy nor the original is resold or otherwise distributed with the intention of earning a profit thereon.

This Article Information Sheet is provided as a courtesy in response to a customer request. A Safety Data Sheet (SDS) has not been prepared for these product(s) because they are articles. Articles are not subject to the Occupational Safety and Health Administration's Hazard Communication Standard (29 CFR 1910.1200(b)(6)(v)). As defined in this standard: "Article" means a manufactured item other than a fluid or particle: (i) which is formed to a specific shape or design during manufacture; (ii) which has end use function(s) dependent in whole or in part upon its shape or design during end use; and (iii) which under normal conditions of use does not release more than very small quantities, e.g., minute or trace amounts of a hazardous chemical, and does not pose a physical hazard or health risk to employees.

Document Group:	34-7684-3	Version Number:	3.05
Issue Date:	06/09/17	Supersedes Date:	02/01/17

SECTION 1: Identification

1.1. Product identifier

Black EPDM Tubing (on plastic core) ==>(LH-A100-1762-5)

Product Identification Numbers

80-6105-9742-1, 80-6105-9752-0, 80-6105-9755-3, 80-6105-9759-5, 80-6105-9760-3, 80-6105-9763-7, 80-6107-3565-8, 80-6107-4803-2, 80-6108-3339-6, 80-6108-3644-9, 80-6109-2831-1, 80-6112-1759-9, 80-6116-1725-1

1.2. Recommended use and restrictions on use

Recommended use

Electrical

1.3. Supplier's details

MANUFACTURER:	3M
DIVISION:	Electrical Markets Division
ADDRESS:	3M Center, St. Paul, MN 55144-1000, USA
Telephone:	1-888-3M HELPS (1-888-364-3577)

1.4. Emergency telephone number

1-800-364-3577 or (651) 737-6501 (24 hours)

SECTION 2: Hazard identification

This product is exempt from hazard classification according to OSHA Hazard Communication Standard, 29 CFR 1910.1200.

SECTION 3: Composition/information on ingredients

Ingredient	C.A.S. No.	% by Wt
Black EPDM tube	Trade Secret*	100

*The specific chemical identity and/or exact percentage (concentration) of this composition has been withheld as a trade secret.

SECTION 4: First aid measures

4.1. Description of first aid measures

Inhalation:

No need for first aid is anticipated.

Skin Contact:

No need for first aid is anticipated.

Eye Contact:

No need for first aid is anticipated.

If Swallowed:

No need for first aid is anticipated.

SECTION 5: Fire-fighting measures

In case of fire: Use a carbon dioxide or dry chemical extinguisher to extinguish.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Not applicable.

6.2. Environmental precautions

Not applicable.

6.3. Methods and material for containment and cleaning up

Not applicable.

SECTION 7: Handling and storage

7.1. Precautions for safe handling

This product is considered to be an article which does not release or otherwise result in exposure to a hazardous chemical under normal use conditions.

7.2. Conditions for safe storage including any incompatibilities

No special storage requirements.

SECTION 8: Exposure controls/personal protection

This product is considered to be an article which does not release or otherwise result in exposure to a hazardous chemical under normal use conditions. No engineering controls or personal protective equipment (PPE) are necessary.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

General Physical Form:	Solid
Odor, Color, Grade:	Black EPDM tube
Odor threshold	<i>Not Applicable</i>
pH	<i>Not Applicable</i>
Melting point	<i>No Data Available</i>
Boiling Point	<i>Not Applicable</i>
Flash Point	No flash point
Evaporation rate	<i>Not Applicable</i>
Flammability (solid, gas)	Not Classified
Flammable Limits(LEL)	<i>Not Applicable</i>
Flammable Limits(UEL)	<i>Not Applicable</i>
Vapor Pressure	<i>Not Applicable</i>
Vapor Density	<i>Not Applicable</i>
Density	<i>No Data Available</i>
Specific Gravity	<i>No Data Available</i>
Solubility in Water	<i>Not Applicable</i>
Solubility- non-water	<i>Not Applicable</i>
Partition coefficient: n-octanol/ water	<i>Not Applicable</i>
Autoignition temperature	<i>Not Applicable</i>
Decomposition temperature	<i>No Data Available</i>
Viscosity	<i>Not Applicable</i>
Molecular weight	<i>Not Applicable</i>

SECTION 10: Stability and reactivity

This material is considered to be non reactive under normal use conditions.

SECTION 11: Toxicological information**Inhalation:**

No health effects are expected

Skin Contact:

No health effects are expected

Eye Contact:

No health effects are expected

Ingestion:

No health effects are expected

Additional Information:

This product, when used under reasonable conditions and in accordance with the directions for use, should not present a health hazard. However, use or processing of the product in a manner not in accordance with the product's directions for use may affect the performance of the product and may present potential health and safety hazards.

SECTION 12: Ecological information

This article is expected to present a low environmental risk either because use and disposal are unlikely to result in a significant release of components to the environment or because those components that may be released are expected to have insignificant environmental impact.

SECTION 13: Disposal considerations

Dispose of contents/container in accordance with the local/regional/national/international regulations.

SECTION 14: Transport Information

For Transport Information, please visit <http://3M.com/Transportinfo> or call 1-800-364-3577 or 651-737-6501.

SECTION 15: Regulatory information

Chemical Inventories

This product is an article as defined by TSCA regulations, and is exempt from TSCA Inventory requirements.

SECTION 16: Other information

NFPA Hazard Classification

Health: 0 Flammability: 1 Instability: 0 Special Hazards: None

National Fire Protection Association (NFPA) hazard ratings are designed for use by emergency response personnel to address the hazards that are presented by short-term, acute exposure to a material under conditions of fire, spill, or similar emergencies. Hazard ratings are primarily based on the inherent physical and toxic properties of the material but also include the toxic properties of combustion or decomposition products that are known to be generated in significant quantities.

Document Group:	34-7684-3	Version Number:	3.05
Issue Date:	06/09/17	Supersedes Date:	02/01/17

DISCLAIMER: The information in this Article Information Sheet (AIS) is believed to be correct as of the date issued. 3M MAKES NO WARRANTIES, EXPRESSED OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR COURSE OF PERFORMANCE OR USAGE OF TRADE. User is responsible for determining whether the 3M product is fit for a particular purpose and suitable for user's method of use or application. Given the variety of factors that can affect the use and application of a 3M product, some of which are uniquely within the user's knowledge and control, it is essential that the user evaluate the 3M product to determine whether it is fit for a particular purpose and suitable for user's method of use or application.

3M provides information in electronic form as a service to its customers. Due to the remote possibility that electronic transfer may have resulted in errors, omissions or alterations in this information, 3M makes no representations as to its completeness or accuracy. In addition, information obtained from a database may not be as current as the information in the AIS available directly from 3M.

3M USA AISs are available at www.3M.com



Safety Data Sheet

Copyright, 2018, 3M Company.

All rights reserved. Copying and/or downloading of this information for the purpose of properly utilizing 3M products is allowed provided that: (1) the information is copied in full with no changes unless prior written agreement is obtained from 3M, and (2) neither the copy nor the original is resold or otherwise distributed with the intention of earning a profit thereon.

Document Group:	11-4628-1	Version Number:	34.05
Issue Date:	02/15/18	Supersedes Date:	01/04/18

SECTION 1: Identification

1.1. Product identifier

3M™ Cable Preparation Kit CC-3 (Bag)

Product Identification Numbers

78-8018-9838-4, 78-8141-5782-8, 80-6105-9300-8

1.2. Recommended use and restrictions on use

Recommended use

Electrical, Solvent soaked pads for cleaning cable.

1.3. Supplier's details

MANUFACTURER:	3M
DIVISION:	Electrical Markets Division
ADDRESS:	3M Center, St. Paul, MN 55144-1000, USA
Telephone:	1-888-3M HELPS (1-888-364-3577)

1.4. Emergency telephone number

1-800-364-3577 or (651) 737-6501 (24 hours)

SECTION 2: Hazard identification

2.1. Hazard classification

Flammable Liquid: Category 4.

Skin Corrosion/Irritation: Category 2.

Skin Sensitizer: Category 1.

Specific Target Organ Toxicity (single exposure): Category 3.

2.2. Label elements

Signal word

Warning

Symbols

Exclamation mark |

Pictograms

**Hazard Statements**

Combustible liquid.

Causes skin irritation.

May cause an allergic skin reaction.

May cause drowsiness or dizziness.

Precautionary Statements**Prevention:**

Keep away from heat/sparks/open flames/hot surfaces. - No smoking.

Avoid breathing dust/fume/gas/mist/vapors/spray.

Use only outdoors or in a well-ventilated area.

Wear protective gloves.

Wash thoroughly after handling.

Contaminated work clothing must not be allowed out of the workplace.

Response:

IF INHALED: Remove person to fresh air and keep comfortable for breathing.

IF ON SKIN: Wash with plenty of soap and water.

If skin irritation or rash occurs: Get medical advice/attention.

Take off contaminated clothing and wash it before reuse.

Call a POISON CENTER or doctor/physician if you feel unwell.

In case of fire: Use a fire fighting agent suitable for flammable liquids such as dry chemical or carbon dioxide to extinguish.

Storage:

Store in a well-ventilated place. Keep container tightly closed.

Keep cool.

Store locked up.

Disposal:

Dispose of contents/container in accordance with applicable local/regional/national/international regulations.

SECTION 3: Composition/information on ingredients

Ingredient	C.A.S. No.	% by Wt
Isoparaffinic Hydrocarbon	64742-48-9	50 - 70
Cotton pads	None	25 - 40
D-LIMONENE	5989-27-5	5 - 20

SECTION 4: First aid measures

4.1. Description of first aid measures**Inhalation:**

Remove person to fresh air. If you feel unwell, get medical attention.

Skin Contact:

Immediately wash with soap and water. Remove contaminated clothing and wash before reuse. If signs/symptoms develop, get medical attention.

Eye Contact:

No need for first aid is anticipated.

If Swallowed:

Rinse mouth. If you feel unwell, get medical attention.

4.2. Most important symptoms and effects, both acute and delayed

See Section 11.1. Information on toxicological effects.

4.3. Indication of any immediate medical attention and special treatment required

Not applicable

SECTION 5: Fire-fighting measures

5.1. Suitable extinguishing media

In case of fire: Use a fire fighting agent suitable for flammable liquids such as dry chemical or carbon dioxide to extinguish.

5.2. Special hazards arising from the substance or mixture

Closed containers exposed to heat from fire may build pressure and explode.

5.3. Special protective actions for fire-fighters

Water may not effectively extinguish fire; however, it should be used to keep fire-exposed containers and surfaces cool and prevent explosive rupture. Wear full protective clothing, including helmet, self-contained, positive pressure or pressure demand breathing apparatus, bunker coat and pants, bands around arms, waist and legs, face mask, and protective covering for exposed areas of the head.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Evacuate area. Keep away from heat/sparks/open flames/hot surfaces. - No smoking. Use only non-sparking tools. Ventilate the area with fresh air. For large spill, or spills in confined spaces, provide mechanical ventilation to disperse or exhaust vapors, in accordance with good industrial hygiene practice. Warning! A motor could be an ignition source and could cause flammable gases or vapors in the spill area to burn or explode. Refer to other sections of this SDS for information regarding physical and health hazards, respiratory protection, ventilation, and personal protective equipment.

6.2. Environmental precautions

Avoid release to the environment.

6.3. Methods and material for containment and cleaning up

Contain spill. Cover spill area with a fire-extinguishing foam. An appropriate aqueous film forming foam (AFFF) is recommended. Remember, adding an absorbent material does not remove a physical, health, or environmental hazard. Collect as much of the spilled material as possible using non-sparking tools. Place in a metal container approved for transportation by appropriate authorities. Clean up residue with an appropriate solvent selected by a qualified and authorized person. Ventilate the area with fresh air. Read and follow safety precautions on the solvent label and SDS. Seal the container. Dispose of collected material as soon as possible in accordance with applicable local/regional/national/international regulations.

SECTION 7: Handling and storage

7.1. Precautions for safe handling

For industrial or professional use only. Keep away from heat/sparks/open flames/hot surfaces. - No smoking. Avoid breathing dust/fume/gas/mist/vapors/spray. Do not get in eyes, on skin, or on clothing. Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Contaminated work clothing should not be allowed out of the workplace. Avoid release to the environment. Wash contaminated clothing before reuse. Avoid contact with oxidizing agents (eg. chlorine, chromic acid etc.)

7.2. Conditions for safe storage including any incompatibilities

Store in a well-ventilated place. Keep container tightly closed. Keep cool. Protect from sunlight. Store away from heat. Store away from acids. Store away from oxidizing agents.

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

Occupational exposure limits

No occupational exposure limit values exist for any of the components listed in Section 3 of this SDS.

8.2. Exposure controls

8.2.1. Engineering controls

No engineering controls required.

8.2.2. Personal protective equipment (PPE)

Eye/face protection

Under normal use conditions, eye exposure is not expected to be significant enough to require eye protection.

Skin/hand protection

Select and use gloves and/or protective clothing approved to relevant local standards to prevent skin contact based on the results of an exposure assessment. Selection should be based on use factors such as exposure levels, concentration of the substance or mixture, frequency and duration, physical challenges such as temperature extremes, and other use conditions. Consult with your glove and/or protective clothing manufacturer for selection of appropriate compatible gloves/protective clothing. Note: Nitrile gloves may be worn over polymer laminate gloves to improve dexterity. Gloves made from the following material(s) are recommended: Nitrile Rubber
Polymer laminate

If this product is used in a manner that presents a higher potential for exposure (eg. spraying, high splash potential etc.), then use of protective coveralls may be necessary. Select and use body protection to prevent contact based on the results of an exposure assessment. The following protective clothing material(s) are recommended: Apron – Nitrile
Apron - polymer laminate

Respiratory protection

An exposure assessment may be needed to decide if a respirator is required. If a respirator is needed, use respirators as part of a full respiratory protection program. Based on the results of the exposure assessment, select from the following respirator type(s) to reduce inhalation exposure:

Half facepiece or full facepiece air-purifying respirator suitable for organic vapors

For questions about suitability for a specific application, consult with your respirator manufacturer.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

General Physical Form:	Solid (Lint-free cloths soaked with liquid)
Specific Physical Form:	Cloth pads soaked in liquid in can or bag
Odor, Color, Grade:	citrus-like odor
Odor threshold	<i>No Data Available</i>
pH	7
Melting point	<i>No Data Available</i>
Boiling Point	380 °F - 480 °F
Flash Point	144 °F [<i>Test Method: Closed Cup</i>]
Evaporation rate	<i>No Data Available</i>
Flammability (solid, gas)	Not Classified
Flammable Limits(LEL)	<i>No Data Available</i>
Flammable Limits(UEL)	<i>No Data Available</i>
Vapor Pressure	< 1 mmHg [<i>@ 25 °C</i>]
Vapor Density	> 1 [<i>Ref Std: AIR=1</i>]
Density	0.76 g/ml
Specific Gravity	0.76 [<i>Ref Std: WATER=1</i>]
Solubility in Water	Nil
Solubility- non-water	<i>No Data Available</i>
Partition coefficient: n-octanol/ water	<i>No Data Available</i>
Autoignition temperature	<i>No Data Available</i>
Decomposition temperature	<i>No Data Available</i>
Viscosity	1.5 centipoise
Molecular weight	<i>No Data Available</i>
Volatile Organic Compounds	Approximately 740 g/l
VOC Less H2O & Exempt Solvents	760 g/l

SECTION 10: Stability and reactivity

10.1. Reactivity

This material may be reactive with certain agents under certain conditions - see the remaining headings in this section.

10.2. Chemical stability

Stable.

10.3. Possibility of hazardous reactions

Hazardous polymerization will not occur.

10.4. Conditions to avoid

Sparks and/or flames

10.5. Incompatible materials

Strong oxidizing agents

10.6. Hazardous decomposition products

<u>Substance</u>	<u>Condition</u>
Carbon monoxide	Not Specified
Carbon dioxide	Not Specified

SECTION 11: Toxicological information

The information below may not be consistent with the material classification in Section 2 if specific ingredient classifications are mandated by a competent authority. In addition, toxicological data on ingredients may not be

reflected in the material classification and/or the signs and symptoms of exposure, because an ingredient may be present below the threshold for labeling, an ingredient may not be available for exposure, or the data may not be relevant to the material as a whole.

11.1. Information on Toxicological effects

Signs and Symptoms of Exposure

Based on test data and/or information on the components, this material may produce the following health effects:

Inhalation:

May be harmful if inhaled.

Respiratory Tract Irritation: Signs/symptoms may include cough, sneezing, nasal discharge, headache, hoarseness, and nose and throat pain.

May cause additional health effects (see below).

Skin Contact:

Skin Irritation: Signs/symptoms may include localized redness, swelling, itching, dryness, cracking, blistering, and pain.

Allergic Skin Reaction (non-photo induced): Signs/symptoms may include redness, swelling, blistering, and itching.

Eye Contact:

Contact with the eyes during product use is not expected to result in significant irritation.

Ingestion:

Physical Blockage: Signs/symptoms may include cramping, abdominal pain, and constipation.

Gastrointestinal Irritation: Signs/symptoms may include abdominal pain, stomach upset, nausea, vomiting and diarrhea.

May cause additional health effects (see below).

Additional Health Effects:

Single exposure may cause target organ effects:

Central Nervous System (CNS) Depression: Signs/symptoms may include headache, dizziness, drowsiness, incoordination, nausea, slowed reaction time, slurred speech, giddiness, and unconsciousness.

Toxicological Data

If a component is disclosed in section 3 but does not appear in a table below, either no data are available for that endpoint or the data are not sufficient for classification.

Acute Toxicity

Name	Route	Species	Value
Overall product	Dermal		No data available; calculated ATE >5,000 mg/kg
Overall product	Inhalation-Vapor(4 hr)		No data available; calculated ATE ₂₀ - 50 mg/l
Overall product	Ingestion		No data available; calculated ATE >5,000 mg/kg
Isoparaffinic Hydrocarbon	Inhalation-Vapor		LC50 estimated to be 20 - 50 mg/l
Isoparaffinic Hydrocarbon	Dermal	Rabbit	LD50 > 3,000 mg/kg
Isoparaffinic Hydrocarbon	Ingestion	Rat	LD50 > 5,000 mg/kg
D-LIMONENE	Inhalation-Vapor (4 hours)	Mouse	LC50 > 3.14 mg/l
D-LIMONENE	Dermal	Rabbit	LD50 > 5,000 mg/kg
D-LIMONENE	Ingestion	Rat	LD50 4,400 mg/kg

ATE = acute toxicity estimate

Skin Corrosion/Irritation

Name	Species	Value
Isoparaffinic Hydrocarbon	Rabbit	Irritant
D-LIMONENE	Rabbit	Mild irritant

Serious Eye Damage/Irritation

Name	Species	Value
Isoparaffinic Hydrocarbon	Rabbit	No significant irritation
D-LIMONENE	Rabbit	Mild irritant

Skin Sensitization

Name	Species	Value
Isoparaffinic Hydrocarbon	Guinea pig	Not classified
D-LIMONENE	Mouse	Sensitizing

Respiratory Sensitization

For the component/components, either no data are currently available or the data are not sufficient for classification.

Germ Cell Mutagenicity

Name	Route	Value
Isoparaffinic Hydrocarbon	In vivo	Not mutagenic
Isoparaffinic Hydrocarbon	In Vitro	Some positive data exist, but the data are not sufficient for classification
D-LIMONENE	In Vitro	Not mutagenic
D-LIMONENE	In vivo	Not mutagenic

Carcinogenicity

Name	Route	Species	Value
Isoparaffinic Hydrocarbon	Dermal	Mouse	Some positive data exist, but the data are not sufficient for classification
Isoparaffinic Hydrocarbon	Inhalation	Human and animal	Some positive data exist, but the data are not sufficient for classification
D-LIMONENE	Ingestion	Rat	Some positive data exist, but the data are not sufficient for classification

Reproductive Toxicity**Reproductive and/or Developmental Effects**

Name	Route	Value	Species	Test Result	Exposure Duration
Isoparaffinic Hydrocarbon	Inhalation	Not classified for development	Rat	NOAEL 2.4 mg/l	during organogenesis
D-LIMONENE	Ingestion	Not classified for female reproduction	Rat	NOAEL 750 mg/kg/day	prematuring & during gestation
D-LIMONENE	Ingestion	Not classified for development	Multiple animal species	NOAEL 591 mg/kg/day	during organogenesis

Target Organ(s)**Specific Target Organ Toxicity - single exposure**

Name	Route	Target Organ(s)	Value	Species	Test Result	Exposure Duration
------	-------	-----------------	-------	---------	-------------	-------------------

Isoparaffinic Hydrocarbon	Inhalation	central nervous system depression	May cause drowsiness or dizziness	Human and animal	NOAEL Not available	
Isoparaffinic Hydrocarbon	Inhalation	respiratory irritation	Some positive data exist, but the data are not sufficient for classification		NOAEL Not available	
Isoparaffinic Hydrocarbon	Inhalation	nervous system	Not classified	Dog	NOAEL 6.5 mg/l	4 hours
Isoparaffinic Hydrocarbon	Ingestion	central nervous system depression	May cause drowsiness or dizziness	Professional judgement	NOAEL Not available	
D-LIMONENE	Ingestion	nervous system	Not classified		NOAEL Not available	

Specific Target Organ Toxicity - repeated exposure

Name	Route	Target Organ(s)	Value	Species	Test Result	Exposure Duration
Isoparaffinic Hydrocarbon	Inhalation	nervous system	Not classified	Rat	LOAEL 4.6 mg/l	6 months
Isoparaffinic Hydrocarbon	Inhalation	kidney and/or bladder	Not classified	Rat	LOAEL 1.9 mg/l	13 weeks
Isoparaffinic Hydrocarbon	Inhalation	respiratory system	Not classified	Multiple animal species	NOAEL 0.6 mg/l	90 days
Isoparaffinic Hydrocarbon	Inhalation	bone, teeth, nails, and/or hair blood liver muscles	Not classified	Rat	NOAEL 5.6 mg/l	12 weeks
Isoparaffinic Hydrocarbon	Inhalation	heart	Not classified	Multiple animal species	NOAEL 1.3 mg/l	90 days
D-LIMONENE	Ingestion	kidney and/or bladder	Not classified	Rat	LOAEL 75 mg/kg/day	103 weeks
D-LIMONENE	Ingestion	liver	Not classified	Mouse	NOAEL 1,000 mg/kg/day	103 weeks
D-LIMONENE	Ingestion	heart endocrine system bone, teeth, nails, and/or hair hematopoietic system immune system muscles nervous system respiratory system	Not classified	Rat	NOAEL 600 mg/kg/day	103 weeks

Aspiration Hazard

Name	Value
Isoparaffinic Hydrocarbon	Aspiration hazard
D-LIMONENE	Aspiration hazard

Please contact the address or phone number listed on the first page of the SDS for additional toxicological information on this material and/or its components.

SECTION 12: Ecological information

Ecotoxicological information

Please contact the address or phone number listed on the first page of the SDS for additional ecotoxicological information on this material and/or its components.

Chemical fate information

Please contact the address or phone number listed on the first page of the SDS for additional chemical fate information on this material and/or its components.

SECTION 13: Disposal considerations

13.1. Disposal methods

Dispose of contents/ container in accordance with the local/regional/national/international regulations.

Incinerate in a permitted waste incineration facility. Proper destruction may require the use of additional fuel during incineration processes. As a disposal alternative, Dispose of waste product in a permitted industrial waste facility. Empty drums/barrels/containers used for transporting and handling hazardous chemicals (chemical substances/mixtures/preparations classified as Hazardous as per applicable regulations) shall be considered, stored, treated & disposed of as hazardous wastes unless otherwise defined by applicable waste regulations. Consult with the respective regulating authorities to determine the available treatment and disposal facilities.

EPA Hazardous Waste Number (RCRA): Not regulated

SECTION 14: Transport Information

For Transport Information, please visit <http://3M.com/Transportinfo> or call 1-800-364-3577 or 651-737-6501.

SECTION 15: Regulatory information

15.1. US Federal Regulations

Contact 3M for more information.

EPCRA 311/312 Hazard Classifications:

Physical Hazards

Flammable (gases, aerosols, liquids, or solids)

Health Hazards

Respiratory or Skin Sensitization

Skin Corrosion or Irritation

Specific target organ toxicity (single or repeated exposure)

15.2. State Regulations

Contact 3M for more information.

15.3. Chemical Inventories

The components of this material are in compliance with the provisions of Australia National Industrial Chemical Notification and Assessment Scheme (NICNAS). Certain restrictions may apply. Contact the selling division for additional information.

The components of this product are in compliance with the new substance notification requirements of CEPA.

The components of this material are in compliance with the China "Measures on Environmental Management of New Chemical Substance". Certain restrictions may apply. Contact the selling division for additional information.

The components of this material are in compliance with the provisions of the Korean Toxic Chemical Control Law. Certain restrictions may apply. Contact the selling division for additional information.

The components of this material are in compliance with the provisions of Philippines RA 6969 requirements. Certain restrictions may apply. Contact the selling division for additional information.

The components of this product are in compliance with the chemical notification requirements of TSCA.

Contact 3M for more information.

15.4. International Regulations

Contact 3M for more information.

This SDS has been prepared to meet the U.S. OSHA Hazard Communication Standard, 29 CFR 1910.1200.

SECTION 16: Other information

NFPA Hazard Classification

Health: 2 **Flammability:** 2 **Instability:** 0 **Special Hazards:** None

National Fire Protection Association (NFPA) hazard ratings are designed for use by emergency response personnel to address the hazards that are presented by short-term, acute exposure to a material under conditions of fire, spill, or similar emergencies. Hazard ratings are primarily based on the inherent physical and toxic properties of the material but also include the toxic properties of combustion or decomposition products that are known to be generated in significant quantities.

HMIS Hazard Classification

Health: *2 **Flammability:** 2 **Physical Hazard:** 0 **Personal Protection:** B

Hazardous Material Identification System (HMIS® IV) hazard ratings are designed to inform employees of chemical hazards in the workplace. These ratings are based on the inherent properties of the material under expected conditions of normal use and are not intended for use in emergency situations. HMIS® IV ratings are to be used with a fully implemented HMIS® IV program. HMIS® is a registered mark of the American Coatings Association (ACA).

Document Group:	11-4628-1	Version Number:	34.05
Issue Date:	02/15/18	Supersedes Date:	01/04/18

Reason for Reissue

Conversion to GHS format SDS.

DISCLAIMER: The information in this Safety Data Sheet (SDS) is believed to be correct as of the date issued. 3M MAKES NO WARRANTIES, EXPRESSED OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR COURSE OF PERFORMANCE OR USAGE OF TRADE. User is responsible for determining whether the 3M product is fit for a particular purpose and suitable for user's method of use or application. Given the variety of factors that can affect the use and application of a 3M product, some of which are uniquely within the user's knowledge and control, it is essential that the user evaluate the 3M product to determine whether it is fit for a particular purpose and suitable for user's method of use or application.

3M provides information in electronic form as a service to its customers. Due to the remote possibility that electronic transfer may have resulted in errors, omissions or alterations in this information, 3M makes no representations as to its completeness or accuracy. In addition, information obtained from a database may not be as current as the information in the SDS available directly from 3M.

3M USA SDSs are available at www.3M.com